

## G18UBR45XX *Series Prestigio Plus*

L-shaped 16" x 24" grab bar, right-handed, painted or chromed stainless steel, polished stainless ends and peg mounting system

Mounting hardware supplied for wood stud installation.

### Product Data


|                            |                        |
|----------------------------|------------------------|
| Overall Dimensions (Inch.) | 20-3/16x2-3/4x26-11/16 |
| Net Weight (lbs.)          | 3.31                   |

### Installation Hardware Details

|                                  |                        |
|----------------------------------|------------------------|
| Stainless steel screw and dowels | Fischer SX 8 6x70 Inox |
|----------------------------------|------------------------|

### Packaging Details

|                              |                           |
|------------------------------|---------------------------|
| Package                      | LDPE bag in cardboard box |
| Package dimensions (Inch.)   | 23-5/8 x 5-11/16 x 4-5/16 |
| Weight with Packaging (lbs.) | 3.97                      |











# G18UBR45XX

Series Prestigio Plus

## Available Finishes (xx)

### Grab bar body

|  |            |  |             |  |           |
|--|------------|--|-------------|--|-----------|
|  D8 | Oxide Gray |  DM | Black Matte |  G9 | Lime      |
|  N1 | Satin      |  N2 | Bright      |  P5 | Aubergine |
|  R2 | Copper     |  W2 | Warm white  |  |           |

### Other parts

|  |        |
|--|--------|
|  C1 | Chrome |
|--|--------|

## Materials and finishes

|                 |          |
|-----------------|----------|
| Stainless Steel | Polished |
| ABS             | Polished |
| Aluminium       | Polished |

## Load Capacity

|          |          |
|----------|----------|
| Vertical | 450 lbs. |
|----------|----------|

## Warning

Before installation and use, read the installation and use instructions in their entirety. If questions arise please contact Ponte Giulio company.

## Cleaning

The device is not affected by the room's temperature, though it must NOT be installed in environments subject to temperatures below 4°C or above 40°C.

Do not install in saunas. Not comply with the indicated temperatures may damage the plastic coating of the device.

## Warranty

Please visit [www.pontegiulio.com](http://www.pontegiulio.com) for complete warranty details.